

## Fast Medium Wave Infrared Emitter for Bodycare




**TOSHIBA ZENIT** heat emitter is designed for body relaxation applications such as Infrared cabin.

Thanks to **TOSHIBA** Infrared technology, fast start will save warm-up time, a compact design will allow installation in narrow spaces, with optimum proportion of infrared spectrum for a totally safe use.

With **TOSHIBA ZENIT** heat emitter, more uniform and relaxing heat can be enjoyed for a perfect wellness.

### Skin penetration depth VS wavelength



### Advantages :


- > Optimum proportion of infrared heat.
- > Fast start without warm up time, energy saving.
- > Compact and easy to install.
- > Healthy and comfortable heat.






# Fast Medium Wave Infrared Emitter for Bodycare

## Type Bf



## Type I


Available **MAGIC FIT**



Désignation	Watts (W)	Volts (V)	Wire length WL1 (mm)	Wire length WL2 (mm)	Connection terminal end	Overall length OAL (mm)	Heating length CL (mm)	Burning Position	Ave. Life Hours	Order number	Technical drawing
JHT 235V 350W 550 BfU	350	235	300 ± 10	1590 ± 25	Splice	626 ± 2	550	Universal	5000	4JHS170	EM-907
JHT 235V 500W 550 BfU	500	235	300 ± 10	1590 ± 25	Splice	626 ± 2	550	Universal	5000		EM-1555
JHT 235V 500W 700 BfU	500	235	300 ± 10	1590 ± 25	Splice	785 ± 2	700	Universal	5000	4JHS025	EM-905
JHT 235V 750W 700 BfU	750	235	300 ± 10	1590 ± 25	Splice	785 ± 2	700	Universal	5000	4JHS169	EM-906

Cables terminal can be modified on request (Faston, fork, end striped, ring...) – For other power or dimension please contact us.

### TOSHIBA ZENIT Emitter IR heat proportion (internal comparison)



Connect to :  
[www.toshiba-lighting.com](http://www.toshiba-lighting.com)

Contact us :  
TOSHIBA LIGHTING PRODUCTS (France)  
42 Rue St Dizier  
54000 Nancy  
Phone : + 33 (0) 3 83 39 00 83